

clamp connection diaphragm seal





Diaphragm seals are designed to isolate the sensing element of pressure gauges and pressure switches from process fluids that may be corrosive, viscous, sedimentous and/or with a high temperature. The diaphragm is welded to the upper body, to ensure separation of the filling fluid from the process medium. Faced diaphragm position enables deep cleaning of the surface while the quick-connection Clamp enables frequent removal from the process during sterilization and cleaning operations, a common requirement in the food processing industry.

4.ALI.4.--- - MGS9/AL

Design: 74-06 SSI.

Working pressure: from 0...15 to 0...600 psi (from 0...1 to 0...40 bar), as from RANGE table .

Process temperature: -4...+212°F (-20°C...+100°C);

Max $284^{\circ}F$ (140 °C) for 30 minutes during cleaning stage (C.I.P.) ¹ and sterilization (S.I.P) ².

Accuracy 3: (add to instrument accuracy) ±0,5% max for direct

Diaphragm: welded, 4 - AISI 316L st.st.

Process connection : 4 - AISI 316 st.st. with finishing Ra $\leq\!0.76~\mu m$

(welded parts included), as per ASME BPE SF3.

Filling liquid: mineral oil (FDA approved) for food industry.

4.ALI.4.TA3- - MGS9/AL - 150°C

Process temperature: -4...+302°F (-20°C...+150°C)

Other features: as Standard Model.

2) S.I.P. = Steamed In Place - available for ranges > 1bar when steam pressure does not exceed the max admissible pressure on the connected instrument

RANGES (1)

Pressure gauges DS	1" Clamp	1" 1/2 Clamp	2" Clamp	2" 1/2 Clamp	3" Clamp
2.5"	0100/0600 psi	060/0600 psi			
(63mm)	(06/040 bar)	(04/040 bar)			
4"		060/0600 psi	030/0600 psi	015/0600 psi	015/0400 psi
(100mm)		(04/040 bar)	(01,6/040 bar)	(01/040 bar)	(01/025 bar)
6"		0100/0600 psi	030/0600 psi	030/0600 psi	030/0400 psi
(150mm)		(06/040 bar)	(02,5/040 bar)	(01,6/040 bar)	(01,6/025 bar)

(1) Vacuum and compound are available upon request



¹⁾ C.I.P. = Cleaned In Place


³⁾ at +68°F (20 °C) process fluid temperature, or state temperature when ordering.


MGS9/AL - STD cod. ----

MGS9/AL - 150°C cod. TA3-

RC5 - 02/16

MERGENTO IMPROVE THEIR PRODUCTION, MESSER, NUOVA FINAR RESERVE THE RIGHT TO THEMSELIVES TO MAKE ALL THE MODIFICATIONS THAT THEY DEEM INDISPRENSEAS ANY TIME. UPDATED DATA-SHEETS REAVALABLE ON SITE: www.m.nuovafina.com





DN Clamp	Code	С	Н	Hd	D	f	M
1"	6T-	1,71"	1,18"	1,18"	1,98"	21F - G 1/4 A	0,78"
1" 1/2	AT-	1,71"	1,37"	1,37"	1,98"	21F - G 1/4 A 41F - G 1/2 A	1,18"
2"	BT-	2,22"	1,37"	1,37"	2,51"	41F - G 1/2 A	1,57"
2" 1/2	DT-	2,77"	1,37"	1,37"	3,05"	41F - G 1/2 A	1,96"
3"	ET-	3,29"	1,37"	1,37"	3,58"	41F - G 1/2 A	2,56"

dimensions: inches

ASSEMBLING

 \boldsymbol{D} - All diaphragm seals are mounted directly on the instruments.

All diaphragm seals are mounted on the instruments and fixed by an aluminium protection label. $\,$


FINISHING

0 - Ra ≤0,76 μm, as per ASME BPE SF1	(1)
A - Ra ≤0,51 μm, as per ASME BPE SF1	(1)
B - Ra < 0.38 um as per ASME BPE SE4 - electropolished	(1)

(1) welded parts included

OPTIONS

C05 - Helium Test	
P04 - Dye penetrant test	



"HOW TO ORDER" SEQUENCE

 $Section/Model/Connection\ material/Version/Diaphragm\ material/Process\ Connection/Finishing/Instrument\ connection/Assembling/Options$

4 ALI

4

.

6T-...ET-

NUOVA FIMA srl

21F - G 1/4 F

D

C05...P04

TA3-

0 A B

41F - G 1/2 F

Copyright © Nuova Fima srl. All rights reserved. Any part of this publication should not be reproduced without a written Nuova Fima's srl approval

